

EBULLIOMETER model Salleron ETH

Quick method for alcohol detection



Perfect combination of TRADITION and INNOVATION

TRADITION

The frame keeps the original technical and productive features, as a guarantee of a perfect thermodynamic balance

ALCOHOL DETECTION %

3 minutes

POWER

52 working hours

Rechargeable battery with micro USB

ELECTRIC HEATING SYSTEM

100 W

TECHNICAL FEATURES

- 220/240 V - 50/60 Hz - 125 W
- Measuring range: 5 - 20 V/V
- Unit of measure: 0,01% V/V
(Measures in ebulliometric range)
- Repeatability: + 0,10
- Tolerance: + 0,10



Easy and intuitive keyboard

INNOVATION

Electronics detect the boiling temperature, calculate the thermal balance point and show the alcoholic value on the display

EXACTA+OPTECH LABCENTER S.p.A.

Via Bosco, 21 - 41030 S. Prospero (MO) - Italy

eno@exactaoptech.com

www.exactaoptech.com